FIGARO

Figaro Oxygen Sensor SK-25F

Features:

- * Virtually no influence from CO₂, CO, H₂S, NO, H₂
- * Temperature compensation circuit included
- * Good linearity
- * No position dependency
- * Stable output signal
- * No external power supply required for sensor operation
- * No warmup time is required

Applications:

- * Safety Air conditioners, oxygen detectors, fire detectors, fuel cell systems
- * Measurement Oxygen monitors in flue gas
- * Biotechnology Oxygen incubators, anaerobic cultivators

GEN SENS

-25F

* Food industry - Refrigeration, greenhouses

The Figaro Oxygen Sensor SK-25F is a unique galvanic cell type oxygen sensor. Its most notable features are no influence from CO2, good linearity up to 30% oxygen, and excellent chemical durability. This feature makes the sensor ideal for oxygen monitoring in various applications such as the biochemical field, food industry, and domestic safety applications.

Sensitivity characteristics (typical values under std. test conditions)

Response time (typical)



Dimensions



u/m: mm If not specified, all tolerances are $\pm 0.2 \mbox{ mm}$

Specifications

Item		Model
		SK-25F
Measurement range		0~30% O2
Accuracy (Note 1)		±1% full scale
Operating conditions	Atmospheric pressure	$1013hPa\pm20\%$
	Temperature	-10°~50°C
	Relative humidity	0~99%RH (no condensation)
Response time (90%) (Note 2)		\leq 15 seconds
Initial output voltage under standard test conditions		5.5~8.5mV
Standard test conditions	Atmospheric pressure	1013 ± 5hPa
	Temperature	20°±1°C
	Relative humidity	60±5%RH
Life expectancy at 20°C in normal air (Note 3)		approx. 3 years

Notes:

 When calibrated at both 0% and 30% of O2, accuracy in the range from 0-30% O2 shall be within ±1% full scale.
Sensors should be used under conditions where the air exchange is greater than 200~300ml/minute in order to obtain the response speed as specified in Table 1.
Life expectancy at 20°C in normal air is defined as the period until sensor output drops to 60% of original value.

NOTE: When the sensor is shipped, blue tape covers the gas diffusion holes to minimize consumption of the sensor life during storage. Before measuring sensor output, the tape should be removed.



FIGARO ENGINEERING INC. 1-5-11 Senba-nishi Mino, Osaka 562-8505 JAPAN Tel: 81-72-728-2567 Fax: 81-72-728-0467 email: figaro@figaro.co.jp www.figaro.co.jp